



TCS INFRA COLOR SAMPLE DYEING MACHINE



Truly we fulfill your wish

BEAKER LOCKING IN CARRIAGE



Main advantages:

- Crease- and spot-free sample dyeing.
- Knitted and woven fabrics as well as yarn can be dyed.
- Cotton, wool and synthetic materials.
- State of the art process controller with large Integrated program memory.
- Low liquor ratio: 1:5 fabric dyeing cotton.
- Stainless steel cabinet.
- Soda ash adding without opening the beakers.
- No glycerin or cooling water needed.
- Very good price / performance value.

Simple operation:

- Filling dye liquor and textile.
- Optional: liquid chemical to be added later on during the dye process.
- Simple fixation of the beakers into the machine.
- Calling of the dye program from memory and starting the dye process.

Beaker support:

- Three-dimensional movement and 360° rotation (clockwise and Counterclockwise) allow even and dyed through samples.

- The multifunctional beaker holder allows the use of different beaker sizes.
- Depending on structure and kind of the material to be dyed, the rotational Speed can be varied between 1 and 50 rotations per minute.

Beaker sizes can be accommodated in 12 x 250ml model:

- 1000 ml x 04 beakers, • 500 ml x 6 beakers, • 250 ml x 12 beakers. • 75ml x 12 beakers, • 100 ml x 12 beakers, • 150 ml x 12 beakers, • 200 ml x 12 beakers

Beaker sizes can be accommodated in 18 x 250ml model:

- 1000 ml x 08 beakers, • 500 ml x 12 beakers, • 250 ml x 18 beakers. • 75ml x 18 beakers, • 100 ml x 18 beakers, • 150 ml x 18 beakers, • 200 ml x 18 beakers

Temperature measuring:

- The measuring of the temperature takes place inside the beakers allowing the direct measurement of the dye liquor. This enables the machine to accurately control and regulate the temperature.

Heating system:

- The laboratory dye machine is equipped with four 0.75 kW or 1 kW (max.) infrared heating tubes.
- Maximal temperature: 140 °C.
- Heating rate can be varied between 0.5 °C/min and 4 °C/min.

Cooling system:

- Air cools down to the required temperature. The machine does not need any cooling water.

Process controller:

- DP-02 dyeing controller
- Display showing dyeing process steps, temperature and rotation direction.
- 50 programs with 32 process steps can be stored inside of the controller memory.

Options:

- Chemical adding system: Into the specially designed chemical add system

liquid chemicals can be filled. During the dye process, the chemical can be directly injected in to the beaker which is automatically added to the dye bath. Therefore the beakers do not have to be opened during the dye process. This allows even dyeing since during dosing the movement of the beaker continues very shortly after the dosing start.

- The standard beaker holder has 12 ,18 and 24 positions.
- To dye yarn we suggest our yarn holder. This accessory is available with extra cost with all combination of beakers.
- Loose stock carrier is also available for dye crease sensitive and delicate materials like silk, wools etc.
- Graphical display touch screen controller can also provide on request.

Specification:

MODEL	12X250ML	18X250ML	24X250ML
HEATING	INFRA RED RAYS	INFRA RED RAYS	INFRA RED RAYS
COOLING	BY AIR	BY AIR	BY AIR
HEATING POWER	3KW	3KW	6KW
COOLING POWER	1/10HP MOTOR	1/10HP MOTOR	1/10HP MOTOR
DRIVE POWER	¼ HP	¼ HP	½ HP
ROTATION (RPM)	0 TO 50	0 TO 50	0 TO 36
AUTOMATION	DP-02	DP-02	DP-02
MAX.TEMPERATURE	145 DEGREE	145 DEGREE	145 DEGREE
MAX.RATE OF HEATING	4 DEGREE	4 DEGREE	4 DEGREE
MAX.RATE OF COOLING	2.5 DEGREE	2.5 DEGREE	2.5 DEGREE
MATERIAL OF BEAKER	S.S 316L	S.S 316L	S.S 316L
MACHINE BODY	S.S 304	S.S 304	S.S 304
ELECTRIC SUPPLY	230V, 1PHASE,16A	230V, 1PHASE,16A	415V, 3PHASE,16A
MACHINE DIMENSIONS	500 X 650 X 770	600 X 650 X 870	720 X 680 X 990
MACHINE NET WEIGHTS	110KGS	135KGS	155KGS
MACHINE GROSS WEIGHTS	175KGS	210KGS	225KGS

Factory : Global Industrial Park, A-14, Survey No: 26/2, Near Nahuli Railway Crossing
Off. N.H. 8, Valwada, VAPI – 396195, Dist: Valsad, Gujarat. E-mail: tcsindustries2012@yahoo.com,
Mob: 09998642044, 09173480650.

RESIDENCE: Plot No: 395, Neela Co-Op.Hsg.Society.Ltd, Near Ambamata Mandir,
Koparli Road, Gunjan, G.I.D.C, VAPI-396195. Mob: 09998642044, 09173480650.